

FEATURES

- Vandal Resistant
- Die-Cast Metal
- Programmable 4 Digit Code
- Designed For High Security Applications
- Wide Operating Temperature Range

RS PRO Die Cast Metal Keypad Lock With LED Indicator

RS Stock No.: 774-8166



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

Our RS PRO Keypad and Proximity Keypad reader is combination of proximity technology and a capacitive keypad which is used for verifying cardholder identification, and access rights validation. This two factor authentication method is designed for high security applications, where both PIN code and a Smart Card are required. PIN code can be enabled for out of hour's operation and disabled during peak times for your convenience. For secure areas it can set to remain active at all times.

General Specifications

Maximum Number of Doors	1
Number of Codes Stored	1000
Status Indicator	LED
Entry Method	Proximity cards, tokens and PIN's
Read range	5cm;
Code Length	4digits
Output Type	1 Relay COM / NO / NC
Operating Frequency	EM 125kHz
Keypad Array	3 x 4
Keypad Material	Die Cast Metal
Keytop Material	Zinc Alloy
Vandal Resistant	Yes

Electrical Specifications

AC or DC Operation	DC
Supply Voltage	12VDC

Mechanical Specifications

Dimensions	120mm x 76mm x 21mm
Height	120mm
Width	76mm
Depth	21mm

Operation Environment Specifications

Operating Temperature	-20°C to 70°C
-----------------------	---------------

Approvals

Compliance/Certifications	2011/65/EU and 2015/863
---------------------------	-------------------------

