

General Information

Extended Product Type:	TY200-40X-100
Product ID:	7TAG054360R0229
EAN:	5414363075240
Catalog Description:	CABLE TIE 40LB 8IN UV BLACK NYLON
Long Description:	Cable Tie, Black Polyamide (Nylon 6.6) for Temperatures up to 105 Degrees Celsius (220 F), Weather and Ultraviolet Resistant for Indoor and Outdoor Applications, UL/EN/CSA62275 Type 2/21 Rated for AH-2 Plenum, Length of 204.72mm (8.06 Inches), Width of 3.556mm (0.140 Inches), Thickness of 1.17mm (0.046 Inches), Tensile Strength Rating of 180 Newtons (40 Pounds), 100 Pack

Categories

Products » Low Voltage Products and Systems » Protection, Connection & Wire Management » Wire Management and Connectivity » Cable Ties

Ordering

EAN:	5414363075240
Minimum Order Quantity:	100 piece
Customs Tariff Number:	3926909995

Dimensions

Product Net Weight:	0.853 g
----------------------------	---------

Container Information

Package Level 1 Units:	100 piece
Package Level 1 Width:	12.7 mm
Package Level 1 Height:	152.4 mm
Package Level 1 Length:	304.8 mm
Package Level 1 EAN:	00786210283364
Package Level 2 Units:	1000 piece
Package Level 2 Width:	127 mm
Package Level 2 Height:	177.8 mm
Package Level 2 Length:	416.56 mm
Package Level 2 EAN:	50786210283369

Additional Information

Brand / Label:	TY-FAST
Product Main Type:	CABLE TIES AND ACCESSORIES
Product Name:	NYLON CABLE TIE
UPC:	786210283364

Certificates and Declarations (Document Number)

Data Sheet, Technical Information: TY200-40X-100

Classifications

ETIM 6:	EC000046 - Cable tie
UNSPSC:	39121703

