



ENGLISH

Constant Current LED Driver 10-54vdc 18 Watt



The RS Pro Range of 18watt Constant current LED Drivers are housed in a compact light weight high quality IP20 plastic enclosure with covered input & output terminals suitable for general Indoor LED applications

Features:

- Input Voltage 100-240Vac
- IP20 Rated
- Low Profile
- Compact Plastic Low Profile enclosure
- 1 Year Warranty
- CE Approved





ENGLISH

Specification

Part Number	1766746
Output Voltage Rating	10-54Vdc
Output Current Range	350mA \pm 6%
Rated Power	18W
Dimensions	141 x 45 x 26mm
Input Voltage Range	100-240Vac
Input Voltage Frequency	50-60Hz
Inrush Current	12A
Efficiency	75%
Overload Protection	100~135% rated output power
Short Circuit Protection	Automatically Restart
Working Temperature	-10°C~40°C
Relative Humidity	20% ~ 95%
MTBF	50k hours
Safety Standards	TUV CE EN 61347 / EN55015