

## Features

- Lightweight and flexible
- Orange colour
- Length 25m
- EN 16436-1 Class 2 / EN 16436-1:2014

## RS PRO Hose Pipe

RS Stock No.: 146-7751, 146-7752, 146-7753



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

**Product Description**

Flexible, smooth, orange hose for liquefied petroleum gas (LPG), propane/butane, to EN 16436-1 Class 2. The hose is primarily for use in assemblies of LPG applications.

For use with barbecues, patio heaters, caravan installations and weed burners.

Important: The European Committee for Standardisation has introduced new standards for LPG hoses: EN16436-1 2014.

**General Specification**

|                               |          |
|-------------------------------|----------|
| Brand                         | RS PRO   |
| Features                      | Flexible |
| Materials                     | EPDM     |
| Colour                        | Orange   |
| Length                        | 25m      |
| Suitable Applications         | Gas      |
| Maximum Operating Temperature | +80°C    |
| Minimum Operating Temperature | -30°C    |
| Hose Pipe Action              | Transfer |
| Bend Radius                   | 40mm     |

**Products in series**

| Stock No. | Lenght | Inner Diameter | Outer Diameter | Colour |
|-----------|--------|----------------|----------------|--------|
| 146-7751  | 25m    | 9,5mm          | 16,5mm         | Orange |
| 146-7752  | 25m    | 12,7mm         | 21,5mm         | Orange |
| 146-7753  | 25m    | 19mm           | 27mm           | Orange |