

## PPS SQKIT - PRE-ASSEMBLED CONFIGURATIONS

### PPS SQ - Kit for Pneumatic Tools

The Prevost PPS SQKIT is a plug and play system (internal Ø 25mm) that distributes compressed air directly to a workstation. Designed to optimize the delivery and control of compressed air systems, the PPS SQKIT embodies quality and reliability, ensuring minimal air loss and maximum performance.



### PRE-ASSEMBLED DESIGN

The PPS SQ Kits deliver all the hallmarks of Prevost's commitment to innovation and quality, offering preassembled solutions that simplify compressed air management. Save time and reduce installation complexity with a plug-and-play solution that's ready to go the moment it's unboxed.

### ALUMINIUM SQUARE PIPE

Compatible with the most common workstation profiles on the market, the square PPS SQ pipe from Prevost is designed and adapted for your workstation, offering 100% aluminium construction for lightness, strength, exceptional quality, and guaranteed leak-free safety.

### EFFICIENCY

The Prevost Filtration units installed on the kits are compact and precise. They guarantee clean air throughout the network which will optimize air flow and extend the service life of your entire system. The PREVOS1 couplings included in the kit, with their innovative design, ensure a perfect seal and provide excellent robustness.

#### Max. operating pressure

10 bar

#### Min. / Max temperature

5 / 50 °C

| Part number             | Length (m) | For pipe OD | ID passage (mm) | Profile   | Net weight (Kg) | Dim. A (mm) | Dim. B (mm) |
|-------------------------|------------|-------------|-----------------|-----------|-----------------|-------------|-------------|
| <b>PPS SQKITPR-MISI</b> | 1.05       | 25 mm       | 6 mm            | ISO 6150B | 4.800           | 1050        | 220         |
| <b>PPS SQKIT-PRMESI</b> | 1.05       | 25 mm       | 7.4 mm          | EUROPEAN  | 4.800           | 1050        | 220         |