

**M18 FUEL™**

M18 FSAG125X-OX

M18 FUEL™ 125 MM ANGLE GRINDER WITH SLIDE SWITCH

- Delivering corded performance similar to a 1200 W grinder
- Reduced gearhead size and lower angle of battery slot - for better balance & ergonomics compared to previous model
- Anti-vibration side handle for lower vibration
- Integrated FIXTEC™ system for tool-free wheel change
- Slim handle design
- Removable dust screen to prevent debris entrance, prolonging motor life
- 125 mm keyless guard for great cutting capacity and fast guard adjustment without using a key
- Line-lock-out function to prevent automatic start up
- The DNA of our FUEL™ platform redefines the balance of cordless technologies. MILWAUKEE®'s POWERSTATE™ brushless motor, REDLITHIUM™ battery pack and REDLINK PLUS™ electronic intelligence delivering outstanding power, run time and durability
- Flexible battery system: works with all MILWAUKEE® M18™ batteries

 **REDLITHIUM™**

No load speed (rpm)	8,500
Brake	No
Anti-kickback protection	Yes
Switch type	Slide lock-on switch
FIXTEC™	Yes
Kit included	No batteries supplied, No charger supplied, HD Box
Article Number	4933478428