

A510 Series Drills Specification

Part No.	Description	Material	Finish	Flute Length	Overall Length	Manf. Dia.
A510*3.0	ADX Drills, Jobber Length	HSS-TiN	TiN	33	61	3
A510*3.1	ADX Drills, Jobber Length	HSS-TiN	TiN	36	65	3.1
A510*1/8	ADX Drills, Jobber Length	HSS-TiN	TiN	36	65	3.18
A510*3.2	ADX Drills, Jobber Length	HSS-TiN	TiN	36	65	3.2
A510*3.3	ADX Drills, Jobber Length	HSS-TiN	TiN	36	65	3.3
A510*3.4	ADX Drills, Jobber Length	HSS-TiN	TiN	39	70	3.4
A510*3.5	ADX Drills, Jobber Length	HSS-TiN	TiN	39	70	3.5
A510*9/64	ADX Drills, Jobber Length	HSS-TiN	TiN	39	70	3.57
A510*3.6	ADX Drills, Jobber Length	HSS-TiN	TiN	39	70	3.6
A510*3.7	ADX Drills, Jobber Length	HSS-TiN	TiN	39	70	3.7
A510*3.8	ADX Drills, Jobber Length	HSS-TiN	TiN	43	75	3.8
A510*3.9	ADX Drills, Jobber Length	HSS-TiN	TiN	43	75	3.9
A510*5/32	ADX Drills, Jobber Length	HSS-TiN	TiN	43	75	3.97
A510*4.0	ADX Drills, Jobber Length	HSS-TiN	TiN	43	75	4
A510*4.1	ADX Drills, Jobber Length	HSS-TiN	TiN	43	75	4.1
A510*4.2	ADX Drills, Jobber Length	HSS-TiN	TiN	43	75	4.2
A510*4.3	ADX Drills, Jobber Length	HSS-TiN	TiN	47	80	4.3
A510*11/64	ADX Drills, Jobber Length	HSS-TiN	TiN	47	80	4.37
A510*4.4	ADX Drills, Jobber Length	HSS-TiN	TiN	47	80	4.4
A510*4.5	ADX Drills, Jobber Length	HSS-TiN	TiN	47	80	4.5
A510*4.6	ADX Drills, Jobber Length	HSS-TiN	TiN	47	80	4.6
A510*4.7	ADX Drills, Jobber Length	HSS-TiN	TiN	47	80	4.7
A510*3/16	ADX Drills, Jobber Length	HSS-TiN	TiN	52	86	4.76
A510*4.8	ADX Drills, Jobber Length	HSS-TiN	TiN	52	86	4.8
A510*4.9	ADX Drills, Jobber Length	HSS-TiN	TiN	52	86	4.9
A510*5.0	ADX Drills, Jobber Length	HSS-TiN	TiN	52	86	5
A510*5.1	ADX Drills, Jobber Length	HSS-TiN	TiN	52	86	5.1
A510*13/64	ADX Drills, Jobber Length	HSS-TiN	TiN	52	86	5.16
A510*5.2	ADX Drills, Jobber Length	HSS-TiN	TiN	52	86	5.2
A510*5.3	ADX Drills, Jobber Length	HSS-TiN	TiN	52	86	5.3
A510*5.4	ADX Drills, Jobber Length	HSS-TiN	TiN	57	93	5.4
A510*5.5	ADX Drills, Jobber Length	HSS-TiN	TiN	57	93	5.5
A510*7/32	ADX Drills, Jobber Length	HSS-TiN	TiN	57	93	5.56
A510*5.6	ADX Drills, Jobber Length	HSS-TiN	TiN	57	93	5.6
A510*5.7	ADX Drills, Jobber Length	HSS-TiN	TiN	57	93	5.7
A510*5.8	ADX Drills, Jobber Length	HSS-TiN	TiN	57	93	5.8
A510*5.9	ADX Drills, Jobber Length	HSS-TiN	TiN	57	93	5.9
A510*15/64	ADX Drills, Jobber Length	HSS-TiN	TiN	57	93	5.95
A510*6.0	ADX Drills, Jobber Length	HSS-TiN	TiN	57	93	6
A510*6.1	ADX Drills, Jobber Length	HSS-TiN	TiN	63	101	6.1
A510*6.2	ADX Drills, Jobber Length	HSS-TiN	TiN	63	101	6.2
A510*6.3	ADX Drills, Jobber Length	HSS-TiN	TiN	63	101	6.3
A510*1/4	ADX Drills, Jobber Length	HSS-TiN	TiN	63	101	6.35
A510*6.4	ADX Drills, Jobber Length	HSS-TiN	TiN	63	101	6.4
A510*6.5	ADX Drills, Jobber Length	HSS-TiN	TiN	63	101	6.5
A510*6.6	ADX Drills, Jobber Length	HSS-TiN	TiN	63	101	6.6
A510*6.7	ADX Drills, Jobber Length	HSS-TiN	TiN	63	101	6.7
A510*17/64	ADX Drills, Jobber Length	HSS-TiN	TiN	69	109	6.75
A510*6.8	ADX Drills, Jobber Length	HSS-TiN	TiN	69	109	6.8

A510 Series Drills Specification

Part No.	Description	Material	Finish	Flute Length	Overall Length	Manf. Dia.
A510*6.9	ADX Drills, Jobber Length	HSS-TiN	TiN	69	109	6.9
A510*7.0	ADX Drills, Jobber Length	HSS-TiN	TiN	69	109	7
A510*7.1	ADX Drills, Jobber Length	HSS-TiN	TiN	69	109	7.1
A510*9/32	ADX Drills, Jobber Length	HSS-TiN	TiN	69	109	7.14
A510*7.2	ADX Drills, Jobber Length	HSS-TiN	TiN	69	109	7.2
A510*7.3	ADX Drills, Jobber Length	HSS-TiN	TiN	69	109	7.3
A510*7.4	ADX Drills, Jobber Length	HSS-TiN	TiN	69	109	7.4
A510*7.5	ADX Drills, Jobber Length	HSS-TiN	TiN	69	109	7.5
A510*19/64	ADX Drills, Jobber Length	HSS-TiN	TiN	75	117	7.54
A510*7.6	ADX Drills, Jobber Length	HSS-TiN	TiN	75	117	7.6
A510*7.7	ADX Drills, Jobber Length	HSS-TiN	TiN	75	117	7.7
A510*7.8	ADX Drills, Jobber Length	HSS-TiN	TiN	75	117	7.8
A510*7.9	ADX Drills, Jobber Length	HSS-TiN	TiN	75	117	7.9
A510*5/16	ADX Drills, Jobber Length	HSS-TiN	TiN	75	117	7.94
A510*8.0	ADX Drills, Jobber Length	HSS-TiN	TiN	75	117	8
A510*8.1	ADX Drills, Jobber Length	HSS-TiN	TiN	75	117	8.1
A510*8.2	ADX Drills, Jobber Length	HSS-TiN	TiN	75	117	8.2
A510*8.3	ADX Drills, Jobber Length	HSS-TiN	TiN	75	117	8.3
A510*21/64	ADX Drills, Jobber Length	HSS-TiN	TiN	75	117	8.33
A510*8.4	ADX Drills, Jobber Length	HSS-TiN	TiN	75	117	8.4
A510*8.5	ADX Drills, Jobber Length	HSS-TiN	TiN	75	117	8.5
A510*8.6	ADX Drills, Jobber Length	HSS-TiN	TiN	81	125	8.6
A510*8.7	ADX Drills, Jobber Length	HSS-TiN	TiN	81	125	8.7
A510*11/32	ADX Drills, Jobber Length	HSS-TiN	TiN	81	125	8.73
A510*8.8	ADX Drills, Jobber Length	HSS-TiN	TiN	81	125	8.8
A510*8.9	ADX Drills, Jobber Length	HSS-TiN	TiN	81	125	8.9
A510*9.0	ADX Drills, Jobber Length	HSS-TiN	TiN	81	125	9
A510*9.1	ADX Drills, Jobber Length	HSS-TiN	TiN	81	125	9.1
A510*23/64	ADX Drills, Jobber Length	HSS-TiN	TiN	81	125	9.13
A510*9.2	ADX Drills, Jobber Length	HSS-TiN	TiN	81	125	9.2
A510*9.3	ADX Drills, Jobber Length	HSS-TiN	TiN	81	125	9.3
A510*9.4	ADX Drills, Jobber Length	HSS-TiN	TiN	81	125	9.4
A510*9.5	ADX Drills, Jobber Length	HSS-TiN	TiN	81	125	9.5
A510*3/8	ADX Drills, Jobber Length	HSS-TiN	TiN	87	133	9.53
A510*9.6	ADX Drills, Jobber Length	HSS-TiN	TiN	87	133	9.6
A510*9.7	ADX Drills, Jobber Length	HSS-TiN	TiN	87	133	9.7
A510*9.8	ADX Drills, Jobber Length	HSS-TiN	TiN	87	133	9.8
A510*9.9	ADX Drills, Jobber Length	HSS-TiN	TiN	87	133	9.9
A510*25/64	ADX Drills, Jobber Length	HSS-TiN	TiN	87	133	9.92
A510*10.0	ADX Drills, Jobber Length	HSS-TiN	TiN	87	133	10
A510*10.1	ADX Drills, Jobber Length	HSS-TiN	TiN	87	133	10.1
A510*10.2	ADX Drills, Jobber Length	HSS-TiN	TiN	87	133	10.2
A510*10.3	ADX Drills, Jobber Length	HSS-TiN	TiN	87	133	10.3
A510*13/32	ADX Drills, Jobber Length	HSS-TiN	TiN	87	133	10.32
A510*10.4	ADX Drills, Jobber Length	HSS-TiN	TiN	87	133	10.4
A510*10.5	ADX Drills, Jobber Length	HSS-TiN	TiN	87	133	10.5
A510*10.6	ADX Drills, Jobber Length	HSS-TiN	TiN	87	133	10.6
A510*10.7	ADX Drills, Jobber Length	HSS-TiN	TiN	94	142	10.7
A510*27/64	ADX Drills, Jobber Length	HSS-TiN	TiN	94	142	10.72

A510 Series Drills Specification

Part No.	Description	Material	Finish	Flute Length	Overall Length	Manf. Dia.
A510*10.8	ADX Drills, Jobber Length	HSS-TiN	TiN	94	142	10.8
A510*10.9	ADX Drills, Jobber Length	HSS-TiN	TiN	94	142	10.9
A510*11.0	ADX Drills, Jobber Length	HSS-TiN	TiN	94	142	11
A510*11.1	ADX Drills, Jobber Length	HSS-TiN	TiN	94	142	11.1
A510*7/16	ADX Drills, Jobber Length	HSS-TiN	TiN	94	142	11.11
A510*11.2	ADX Drills, Jobber Length	HSS-TiN	TiN	94	142	11.2
A510*11.3	ADX Drills, Jobber Length	HSS-TiN	TiN	94	142	11.3
A510*11.4	ADX Drills, Jobber Length	HSS-TiN	TiN	94	142	11.4
A510*11.5	ADX Drills, Jobber Length	HSS-TiN	TiN	94	142	11.5
A510*29/64	ADX Drills, Jobber Length	HSS-TiN	TiN	94	142	11.51
A510*11.6	ADX Drills, Jobber Length	HSS-TiN	TiN	94	142	11.6
A510*11.7	ADX Drills, Jobber Length	HSS-TiN	TiN	94	142	11.7
A510*11.8	ADX Drills, Jobber Length	HSS-TiN	TiN	94	142	11.8
A510*11.9	ADX Drills, Jobber Length	HSS-TiN	TiN	101	151	11.9
A510*15/32	ADX Drills, Jobber Length	HSS-TiN	TiN	101	151	11.91
A510*12.0	ADX Drills, Jobber Length	HSS-TiN	TiN	101	151	12
A510*12.1	ADX Drills, Jobber Length	HSS-TiN	TiN	101	151	12.1
A510*12.2	ADX Drills, Jobber Length	HSS-TiN	TiN	101	151	12.2
A510*12.3	ADX Drills, Jobber Length	HSS-TiN	TiN	101	151	12.3
A510*31/64	ADX Drills, Jobber Length	HSS-TiN	TiN	101	151	12.3
A510*12.4	ADX Drills, Jobber Length	HSS-TiN	TiN	101	151	12.4
A510*12.5	ADX Drills, Jobber Length	HSS-TiN	TiN	101	151	12.5
A510*12.6	ADX Drills, Jobber Length	HSS-TiN	TiN	101	151	12.6
A510*12.7	ADX Drills, Jobber Length	HSS-TiN	TiN	101	151	12.7
A510*1/2	ADX Drills, Jobber Length	HSS-TiN	TiN	101	151	12.7
A510*12.8	ADX Drills, Jobber Length	HSS-TiN	TiN	101	151	12.8
A510*12.9	ADX Drills, Jobber Length	HSS-TiN	TiN	101	151	12.9
A510*13.0	ADX Drills, Jobber Length	HSS-TiN	TiN	101	151	13
A510*14.0	ADX Drills, Jobber Length	HSS-TiN	TiN	108	160	14