



### Main

|                           |  |
|---------------------------|--|
| Range                     | TeSys  |
| Device short name         | GVAE   |
| Product or component type | Auxiliary contact block  |
| Product compatibility     | GV2L<br>GV2LE<br>GV2ME<br>GV2P<br>GV2RT<br>GV3L<br>GV3P<br>LS1D323 |
| Pole contact composition  | 2 NO   |
| Connections - terminals   | Spring terminals 2 cable 0.75...1.5 mm <sup>2</sup>                |
| Quantity per set          | Set of 10  |

### Complementary

|   |  |
|---|--|
| Mounting location                           | Front side   |
| [Ui] rated insulation voltage               | 250 V - conforming to IEC 60947-1<br>300 V - conforming to UL 508<br>300 V - conforming to CSA C22.2 No 14   |
| [Ue] rated operational voltage              | 24...240 V AC<br>24...60 V DC  |
| [Ith] conventional free air thermal current | 2.5 A  |
| Protection type                             | GG fuse <= 10 A<br>GB2CB06 circuit breaker <= 10 A   |
| Mechanical durability                       | 100000 cycles  |
| Rated operational power in VA               | 120 VA at 110...120 V AC-15 - electrical durability: 100000 cycles<br>120 VA at 230...240 V AC-15 - electrical durability: 100000 cycles<br>48 VA at 24 V AC-15 - electrical durability: 100000 cycles<br>60 VA at 48 V AC-15 - electrical durability: 100000 cycles |
| Rated operational power in W                | 15 W at 48 V DC-13 - electrical durability: 100000 cycles<br>24 W at 24 V DC-13 - electrical durability: 100000 cycles<br>9 W at 60 V DC-13 - electrical durability: 100000 cycles   |
| Tightening torque                           | <= 1.4 N.m - on screw clamp terminals  |
| Height                                      | 10 mm  |
| Width                                       | 44.5 mm  |
| Depth                                       | 15 mm  |
| Product weight                              | 0.03 kg  |

### Environment

|                              |                    |
|------------------------------|--------------------|
| environmental characteristic | Normal environment |
|------------------------------|--------------------|

### Contractual warranty

|                 |           |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|