



54V XR FLEXVOLT Reciprocating Saw – 2 X 6Ah

DCS389T2-QW

54V XR FLEXVOLT, Power of the Cord
DEWALT Brushless Motor for power, extended run-time, reliability & durability

Intelligent variable speed trigger and lock off switch
Two position blade clamp allows for flush cutting and increased versatility

Lever action keyless blade clamp for tool-free blade change



Sound Power	95 dB(A)
-------------	----------

Sound Pressure Uncertainty	5 dB(A)
----------------------------	---------

Sound Pressure	84 dB(A)
----------------	----------

Uncertainty K 3 (Vibration)	1.5 m/s ²
-----------------------------	----------------------

Uncertainty K 2 (Vibration)	1.5 m/s ²
-----------------------------	----------------------

Battery Capacity	6 Ah
------------------	------