



## ARCANOL-MULTI3-25KG [📄](#)

Bearing grease

Multi-purpose grease ARCANOL-MULTI3

### Technical information

#### Your current product variant

Grease category	MP	Multi-purpose greases
Package size	25 KG	25 kg hobbock

#### Technical data

$\vartheta_{O \min}$	-30 °C	Operating temperature, min.
$\vartheta_{O \max}$	120 °C	Operating temperature, max.
$\vartheta_G$	75 °C	Upper continuous limit temperature
$n \cdot d_M$	500.000 mm/min	Speed of rotation specific value
	Lithium soap	Thickener type
	Mineral oil	Base oil type
$\nu_{40}$	110 mm <sup>2</sup> /s	Base oil viscosity at +40°C
$\nu_{100}$	12 mm <sup>2</sup> /s	Base oil viscosity at +100 °C
	3	NLGI class
	Multi-purpose grease	Grease category
$\rho$	0,95 kg/dm <sup>3</sup>	Density
	25 kg hobbock	Container
$\approx m$	26,6 kg	Weight