

Features

- Medium Duty
- Industrial castor
- Rotation Swivel
- Fixing Plate
- Rubber
- Corrosion Resistant
- Impact Resistant
- Shock Absorbing

RS PRO Castor Wheels

RS Stock No.: 0631151



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description









Grey no-marking rubber wheel 83 Shore A with black thermoplastic material centre. Hub on plain bore. In zinc-chromium plated pressed steel, turning on double rim of balls. Assembled with self-locking nut. Dust cover ring on the balls.

General Specifications

Rotation	Swivel
Weight Class	Medium Duty
Load Capacity (Kg)	70
Load Capacity / 4pcs (Kg)	280
Tyre Material	Rubber
Hub Material	Thermoplastic
Bracket Material	Pressed Steel
Includes Brake	No
Features	Corrosion Resistant, Impact Resistant, Shock Absorbing
Applications	Industrial castor

Operation Environment Specifications

Operating Temperature (Celsius)	-20° to 80°
----------------------------------------	-------------

							
100x30	100x85	80x60	8,5x12	37	128	70	90

Mechanical Specifications

Mounting Type	Single Bolt
Wheel Diameter (mm)	100
Wheel / Tread Width (mm)	30
Overall Height (mm)	128
Number of Fixing Holes	4
Fixing Hole Size (mm)	8.5x12
Hub Bearing Type	Plain Bore
Thread Size (M)	
Stem Height (mm)	
Stem Diameter (mm)	
Hardness of Wheel (Shore A)	83
Levelling Extent (mm)	
Offset (mm)	37
Castor Weight (Kg)	0.744

Fixing Centres Specifications

Fixing Centres (mm)	80x60
Fixing Centres Length (mm)	80
Fixing Centres Width (mm)	60

Fixing Plate Specifications

Fixing Plate Dimensions (mm)	100x85
Fixing Plate Length (mm)	100
Fixing Plate Width (mm)	85