

Indicator light, 16 mm, round, plastic, blue, smooth, for inscription with insert caps



Figure similar

|   |                      |
|---|----------------------|
| <b>product brand name</b>   | SIRIUS               |
| <b>product designation</b>  | Indicator lights     |
| <b>design of the product</b>  | Single device round  |
| <b>product type designation</b>                                       | 3SB2                 |
| <b>Enclosure</b>  |                      |
| <b>number of command points</b>                                       | 0                    |
| <b>Actuator</b>   |                      |
| <b>design of the actuating element</b>                                | indicator light      |
| <b>product extension optional light source</b>                        | No                   |
| <b>color of the actuating element</b>                                 | blue                 |
| <b>material of the actuating element</b>                              | plastic              |
| <b>shape of the actuating element</b>                                 | Smooth lens          |
| <b>outer diameter of the actuating element</b>                        | 19 mm                |
| <b>type of unlocking device</b>                                       | without              |
| <b>number of switching positions</b>                                  | 0                    |
| <b>Front ring</b>   |                      |
| <b>product component front ring</b>                                   | No                   |
| <b>Holder</b>   |                      |
| <b>material of the holder</b>   | Plastic              |
| <b>General technical data</b>   |                      |
| <b>product function</b>   |                      |
| • EMERGENCY OFF function  | No                   |
| • EMERGENCY STOP function   | No                   |
| <b>protection class IP</b>  | IP65                 |
| <b>vibration resistance according to IEC 60068-2-6</b>                | 20 ... 200 Hz: 5g    |
| <b>reference code according to IEC 81346-2</b>                        | P                    |
| <b>Substance Prohibitance (Date)</b>                                  | 07/01/2006           |
| <b>Net Weight</b>   | 0.003 kg             |
| <b>Connections/ Terminals</b>   |                      |
| <b>tightening torque of the screws in the bracket maximum</b>         | 0.4 N·m              |
| <b>Ambient conditions</b>   |                      |
| <b>ambient temperature</b>  |                      |
| • during operation  | -25 ... +70 °C       |
| • during storage  | -40 ... +80 °C       |
| <b>environmental category during operation according to IEC 60721</b> | 3K6                  |
| <b>Installation/ mounting/ dimensions</b>                             |                      |
| <b>fastening method</b>   | front plate mounting |

|                                   |       |
|-----------------------------------|-------|
| shape of the installation opening | round |
| mounting diameter                 | 16 mm |
| mounting height                   | 9 mm  |
| installation width                | 19 mm |
| installation depth                | 50 mm |

#### Approvals Certificates

|             |                          |                   |
|-------------|--------------------------|-------------------|
| Environment | General Product Approval | Test Certificates |
|-------------|--------------------------|-------------------|

[Environmental Confirmations](#)



[Miscellaneous](#)

|                   |       |
|-------------------|-------|
| Test Certificates | other |
|-------------------|-------|

[Type Test Certificates/Test Report](#)

[Special Test Certificate](#)



[Confirmation](#)

#### Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SB2001-6CF06>

Cax online generator

<https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SB2001-6CF06>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3SB2001-6CF06>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

[https://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3SB2001-6CF06&lang=en](https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SB2001-6CF06&lang=en)

last modified:

4/2/2025