

## MANHATTAN S3 SRC



NYLON MESH/NUBUCK LEATHER SHOES - S3 HRO SRC

Ref. MANHATTANS3



### Product specifications

Upper: Suede split leather (cowhide), S3 water resistant treatment with front rubber reinforcement.  
Lining: Polyester non-woven and knitted mesh. Insock: Removable premolded - Polyester on EVA. Outsole: Cemented - Phylon. Outsole: Rubber. Non metallic shoe.

#### COLOUR

Black-Yellow

#### SIZE

39, 40, 41, 42, 43, 44, 45, 46, 47

### Product Use - Risks



Antistatic



Heat



Slip



Shock



PERFORATION



Second work / craftman



Services / Logistics



Light industry

Product's highlights & user's benefits



RUBBER NITRILE OUTSOLE

Good resistance to abrasion and contact heat  
(HRO = 300°C for 1 minute)  
Optimum adhesion

WELDED SOLE WITH PHYLON MIDSOLE (EVA)

Incomparable comfort and lightness



Quilted collar and tongue

Reduction of pressure points at the lacing



Outsole with protection rubber toe bumper

Reinforced protection of the forefoot



Rear support of the reflective upper

Optimal stabilisation of the foot when walking  
Increased visibility

Anti-slide on the inside of the shoe

Improved heel hold  
Reinforced rear section

Preformed and removable EVA insole

Reinforced ergonomics and comfort in foot movements  
Easy drying



COMPOSITE



Composite toe cap 200j Lightweight and less fatigue  
Non conductive hot and cold



NON METALLIC Compatible with security checks (metal detectors)



Anti-perforation composite protective midsole  
Increased flexibility at the metatarsal level

## Certifications and Standards



REGULATION (EU) 2016/425

EN ISO 20344:2011 Personal protective equipment - Test methods for footwear

EN ISO 20345:2011 Personal protective equipment - Safety footwear.  
S3 HRO: Additional special requirements  
SRC: Slip resistance

## References

References	Bar code	COLOUR	SIZE		
MANHAS3NJ40	3295249230531	Black-Yellow	40	10	-
MANHAS3NJ41	3295249230548	Black-Yellow	41	10	-
MANHAS3NJ42	3295249230555	Black-Yellow	42	10	-
MANHAS3NJ43	3295249230562	Black-Yellow	43	10	-
MANHAS3NJ44	3295249230579	Black-Yellow	44	10	-
MANHAS3NJ45	3295249230586	Black-Yellow	45	10	-
MANHAS3NJ46	3295249230593	Black-Yellow	46	10	-
MANHAS3NJ47	3295249230609	Black-Yellow	47	10	-
MANHAS3NJ39	3295249230432	Black-Yellow	39	10	-