
2101 : Stainless Steel Pipe Cutter 10-90 mm





Description

Max. thickness: 5 mm.
Excellent weight distribution giving improved inertia and providing high stiffness. Thrust ball bearing prevents slider wear and reduces the turning torque of the screw.

Ref. 210125 : Also works on steel pipes with cutting wheels 210121 fitted.

Ref. 210110 - 210130 : Steel pipe cutter (supplied with a steel cutting wheel). Also works on stainless steel pipes with cutting wheels 210123 fitted.

References

Sku	A mm	A " OD	L mm	H mm	E maxi mm	kg
210110			310	118	5	1,740
210125			400	150	5	3,020
210130	27 - 90	3/4 - 3	460	177	5	4,220

