



R-075

Waterproof PVC-coated long gauntlet-style impact gloves, for advanced chemical protection

Waterproof PVC-coated long gauntlet-style impact gloves, for advanced chemical protection

- **Advanced defenses:** RINGERS® R075 impact protection gloves' TPR (thermoplastic rubber) design, developed with F3 Technology™, comfortably protects the top of the hand and full length of the fingers
- **Specialized protection:** Tested against EN 374-1 Type A chemical resistance standards, these RINGERS® gloves guard against various hazards*
- **Added safety:** With a protective inner liner, they satisfy ANSI/ISEA 105-2024 CUT A3 and EN ISO C standards
- **Enhanced grip and durability:** These chemical-resistant gloves feature a textured palm and PVC coating, boosting grip and durability, and meeting ANSI/ISEA 105-2024 and EN ABRASION LEVEL 4



Industries

- Automotive
- Infrastructure Maintenance
- Maintenance
- Oil and gas
- Chemical

Applications

- Drilling assembly and completion
- Handling jagged metal
- Mixing or loading chemicals
- Body painting including surface inspection
- Applying sealers, touching up
- Oil, fluids and filter change
- Spill or leakage cleanup
- Plating, coating, sealing, painting
- Hydraulic repair
- Use of binding agents
- Smelting and cleaning of equipment
- Re-fuel oil fluid and diesel
- Filling, blending and charging of raw materials
- Opening furnaces draining pumps valves or lines and crackers BTX process
- Unexpected leakages spills or other releases



R-075

Waterproof PVC-coated long gauntlet-style impact gloves, for advanced chemical protection

Key Features

- **Patented TPR design:** Finger-length and top-of-hand impact protection
- **PVC coating:** Waterproof defenses against various chemical hazards*
- **Protective inner liner:** For 360° cut resistance

*CE-rated for EN 374-1: A (Methanol) J (n-Heptane) K (Sodium Hydroxide 40%) L (Sulfuric Acid 96%) M (Nitric Acid 65%) O (Ammonium Hydroxide 25%)



Performance Standards

ANSI/ISEA 105-2024



ANSI/ISEA 138-2019



EN388: 2016



4X41CP

EN ISO 374-1:2016



KLMOPT

EN ISO 374-5:2016



Specifications

BRAND STYLE	DESCRIPTION	SIZE	LENGTH	COLOR	PACKAGE
RINGERS® R075	Liner Material: Aramid & glass fiber Coating Material: PVC	8, 10, 12	S/370MM/14.5inches, L/456MM/18inches, 2XL/465MM/18Inches	Red	12 pairs/bag, 2 bags/carton

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 210
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Bldv. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada Inc.
105, rue Lauder
Cowansville (Québec)
J2K 2K8, Canada
T: 1 800 363-8340
F: 1 888 267-3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending:
www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

