

Features

- Spring loaded swivel castors retract when weight is applied
- Dome covers have high grip rubber wrap-around bumpers
- Effortless manoeuvrability
- Safe 280mm deep anti-slip ribbed rubber treads
- Platform size 280 x 380mm
- Continuous hand and guardrail for safety
- Robust tubular steel construction
- Hard wearing powder coated finish in a choice of colours

RS PRO 3 Tread Blue Steel Trade Mobile Step

RS Stock No.: 0285112



Representative image of product

RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

Steel narrow aisle step, widely used in office, library and archiving environments. Strong sprung castors lock and hold in place when weight is applied. The zero turning circle makes them easy to manoeuvre in tight spaces. Long double handrails and a guard railed top tread provide extra assurance for users.

**Not suitable for outdoor use*

General Specifications

Max Load	150kg
Material	Steel
Commodity Code	7326903000
Country of Origin	UK
Recommended Usage	Regular

Similar Products

SKU	Treads	Platform Height (m)	Approx. Working Height1(m)	Height (m)	Width (m)	Depth (m)	Weight (kg)
0285111	2	0.51	2.26	1.19	0.58	0.62	12
0285112	3	0.76	2.51	1.43	0.58	0.8	14
0285114	4	1.02	2.77	1.68	0.58	0.96	17
0285115	5	1.27	3.02	1.94	0.58	1.12	20