

Angle Grinder XGT® 125mm

GA013G

40V max • 125 mm • 8 500 min⁻¹

Efficient brushless tool with paddle switch for cutting and grinding

A compact, brushless angle grinder with paddle switch and 125 mm blade diameter for demanding professional use. The machine features standard electronics, electronic brake, overload protection and AFT-active feedback detection technology.



Technical specifications

Nominal Battery Voltage	40 V
Voltage XGT	✓
Brushless Motor	✓
No load speed	8500 min ⁻¹
Spindle Thread	M14
Bore Size (Arbor Diameter)	22,23 mm
Disc Diameter	125 mm
Anti-Restart Function (NVR Switch)	✓
Electronic brake	✓
Sound Power Level (L _{WA})	93 dB(A)
Sound Pressure Level (L _{pA})	85 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Tool weight with battery	3,2 - 4,5 kg
Product Dimensions (L x W x H):	410 x 140 x 168

User benefits

- Outperforming performance and efficiency similar to corded 1 000 W class grinder
- Active Feedback sensing Technology (AFT) stops the engine if the rotation suddenly stops
- Electric brake for maximum productivity and increased operator safety
- Brushless maintenance-free and long-life motor
- Paddle switch; Easy-to-hold slim grip achieved by optimised parts allocation
- Slim body design for a good grip
- Anti-restart function minimises accidental start-up
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- Side grip can be positioned on both sides for operator convenience
- Spindle lock for easy wheel changes
- Battery protection system automatically shuts off power when the battery level is low
- Soft start for smooth start-ups

Link to product - www.makitauk.com



Related products

Optional AC

158237-4

Grip 36 complete



191G06-2

Dust collecting cover set



199710-5

Wheel Guard Cover 125 mm



347480-2

Wheel cover 125 mm



782423-1

Lock nut wrench 35



Other

User manual

Parts drawing