



Part Number : [2042201110](#)

Product Description : Squba Sealed Receptacle Assembly, 1.80mm Pitch, Single Row, 10 Circuit Housing, Circuit #10 Voided

Series Number : 204220

Status : Active

Product Category : Connector Housings



Documents & Resources

Drawings

[2042201110_sd.pdf](#)

[2042200000-PK-000.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications

[2042200000-AS-000.pdf](#)

[2042200000-PK-000.pdf](#)


[2042200000-PS-000.pdf](#)

[2042200000-TS-000.pdf](#)

[2042201000-TS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Dodecamethylcyclohexasiloxane; Decamethylcyclopentasiloxane;

	Octamethylcyclotetrasiloxane per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	204220
Description	Squba Sealed Receptacle Assembly, 1.80mm Pitch, Single Row, 10 Circuit Housing, Circuit #10 Voided
Application	Power, Signal, Wire-to-Wire
Product Name	Squba
UPC	191128739436

Agency

UL	E29179
----	--------

Physical

Circuits (maximum)	10
Color - Resin	Black

Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	4.670/g
Number of Rows	1
Packaging Type	Tray
Panel Mount	No
Pitch - Mating Interface	1.80mm
Pitch - Termination Interface	1.80mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +105°C

Mates With / Use With

Mates with Part(s)

Description	Part Number
Squba Sealed Plug Assembly, 1.80mm Pitch, Single Row, 10 Circuits	<u>2042230010</u>
Squba Sealed Panel Mount Plug Assembly, 1.80mm Pitch, Single Row, 10 Circuits	<u>2042230110</u>
Squba Sealed Plug Assembly, 1.80mm Pitch, Single Row, 10 Circuit Housing, Circuit #10 Voided	<u>2042231110</u>
Squba Sealed Plug Assembly, 1.80mm Pitch, Single Row, 10 Circuit Housing, All Circuits Voided	<u>2042239910</u>

Use with Part(s)

Description	Part Number
Squba 1.8 Receptacle Terminal, Matte Tin Plating, 24-22 AWG	<u>2043010001</u>

This document was generated on Nov 06, 2025