

WPM02

Outdoor Connect-2 Mini Box

Features & Benefits

- Tough and durable housing
- Multiple appliance cable outlets
- Spacious design suitable for all 13 amp BS plugs and selective timers
- Ideal for transformer linked garden lighting and other outdoor appliances
- IP66 weatherproof rating
- Keyhole slot for temporary locating and in situ alignment



Technical Data

Operating Voltage	230V AC (Socket Strip)
Frequency	50Hz (Socket Strip)
Installation Type	Surface
Earth Class Rating	Class I (Socket Strip)
Operating Temperature	-20°C to 40°C
Ingress Protection Rating	IP66
Socket Outlet	x2 UK Plug Sockets 13A (On Strip)
Mounting Hole Centres (mm)	134 (Top Set, 117 (Bottom Set)
Cable Entry(s)	x3 Flex Cable Entries

General

Data sheet

WPM02

Safety / Weathersafe Outdoor Power

Weight (g)	800
Height (mm)	225
Width (mm)	155
Depth (mm)	107
Body Construction	Polycarbonate
Product Colour	Grey
Accessories (Included)	2 Gang Socket Strip, Velcro pads
EAN Number	5012483010068
Guarantee Period	3 Years

Line Diagrams

