




RJXS8FP25HPE

- SERIES PREFIX
- CONTACT LAYOUT (RJ45 STYLE)
- GENDER
- THERMOPLASTIC 3.8mm to 5.0mm WITH CAP
- TRANSMISSION CLASS (CAT5e)
- HORIZONTAL MOUNT (PCB THRU HOLE)
- POTTED
- WITH EMI/RFI SHIELD

UNLESS OTHERWISE SPECIFIED TOLERANCE TO BE:				THIS DOCUMENT IS THE PROPERTY OF AMPHENOL AUSTRALIA PTY. LTD. NO PART THEREOF MAY BE REPRODUCED AND USED WITHOUT THE PRIOR WRITTEN CONSENT OF THE OWNER				Amphenol Amphenol Australia Pty. Ltd. 22 Industry Blvd Carrum Downs, VIC 3201							
LINEAR		ANGULAR		MATERIAL:		DRN: J.W		DATE: 24/12/2024		TITLE:		PART No:		REV:	
X ±10		X° ±1		SEE COMPONENTS		CKD: P.M.		DATE: 24/12/2024		XLNet, HORZ, IP65, POTTED, SHIELDED, W/ CAP, PANEL THICKNESS 3.8-5.0		RJXS8FP25HPE		1	
X.X ±5		X°X' ±30'													
X.XX ±1		X°XX' ±15'													
BREAK ALL SHARP EDGES AND REMOVE ALL BURRS				FINISH: SEE COMPONENTS		APP'D: P.M.		DATE: 24/12/2024		DRAWING No:		55011542-000-1		SHEET 2/2	
DO NOT SCALE															
DIMENSIONS IN MILLIMETRES						SCALE: NTS		SIZE: A3							