

580

Horn / Light Combination



- Horn / light combination

Technical specifications:

Housing:

ABS, high impact, grey

Cap:

Polycarbonate, transparent

Socket:

B 15 d / 7 Watt

Terminal:

Apparatus clamp 1.5 mm²

Cable entry up to 9 mm ø

Duty cycle:

100 % ED

Bulb included in assembly

- Can be triggered separately

Order specifications:

| Order No. | Voltage (V) | Rated current |
|-------------|-------------|---------------|
| 580 □ 52 54 | 12 V = | 610 mA |
| 580 □ 52 55 | 24 V = | 320 mA |
| 580 □ 52 65 | 24 V ~ | 320 mA |
| 580 □ 52 68 | 230 V ~ | 50 mA |



1 = red

3 = yellow

Other cap colours and voltages available on request.

