

Features

- Designed for a group of employees to lockout equipment with 5 lockout points.
- Small, lightweight design makes it more convenient than traditional lock boxes, allowing for easy handling and storage.
- Provides 5 holes for lockout padlocks and 5 hooks for hanging keys or locks, enabling organized storage.
- Features a clear cover, allowing users to view keys and locks inside the box without opening it.
- Keys inside the box are only accessible after all locks are removed, ensuring a controlled and secure lockout process.
- Comes with pre-drilled holes and wall mounting hardware for simple installation in a central location.

RS PRO PVC Compact Group Lock Box

RS Stock No.: 0276136



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

- *Efficient way for a group of employees to lockout equipment that has multiple lockout points.*
- *Wall mount group lock boxes create a central location for group lockouts throughout your facility.*
- *Small, lightweight size and versatile operation make this clearly more convenient than traditional lock boxes.*
- *5 holes are provided for installing 5 lockout padlocks.*
- *5 hooks are provided for hanging keys/locks.*
- *Clear cover to view keys/locks inside.*
- *Keyhole slot makes it easy to add keys to the box after it has been locked out.*
- *Keys are not accessible until every lock is removed and door slides open.*
- *After all personal locks are removed from exterior lock slots, swing open the door of the group lock box to retrieve the items stored inside.*
- *Pre-drilled holes allow for easy wall mounting. (Wall mounting hardware included)*

General Specifications

Type	Group Lock Box
Material	Base: ABS Cover: Polycarbonate
Number of Locks	5
Colour	Yellow Base with Clear Cover

Mechanical Specifications

Dimensions (H X W X D)	149.5mm x 149.5mm x 55.2mm
Height	149.5mm
Width	149.5mm
Depth	55.2mm
Weight	250 grams

Operation Environment Specifications

Withstand temperature	Max. Service Temperature: 100°C Min. Service Temperature: -20°C
-----------------------	--