

Features

- 1 Gang
- Switched
- Double Pole
- Urea Mouldings
- White
- Stylish smooth profile plate

RS PRO Plug Sockets

RS Stock No.: 0845485



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

- Fits standard 25mm 1 gang back boxes
- Double pole switched
- Urea mouldings make the socket suitable for use in applications where Antibacterial & Antiviral Certified material is required
- Suitable for use with standard UK 13A plug tops

General Specifications

Plate Dimensions (mm)	86 (W) x 86 (H) x 9.5 (D)
Plate Fixing Centres (mm)	60.3
Style	Rounded Profile
Anti Microbial Certified	Yes
Warranty (Years)	25

Mechanical Specifications

Termination Type	Screw
Terminal Size (mm)	Ø5
Terminal Torque Value (Nm)	2
Terminal Capacity - Solid (mm²)	3 x 2.5 or 2 x 4
Twin Earth Terminals	No
Double Pole Switch	Yes
Minimum Back Box Depth (mm)	25
Ingress Protection	IP20
Operational Temperature (°C)	-5 to +40

Electrical Specifications

Frequency (Hz)	50
Resistive Load Rating (A)	13

Approvals

Standards Met	BS 1363-2
---------------	-----------