

Targan™

900/1800/1900 MHz Fixed Mount Antenna

Features

- ✓ External Mount Antenna
- ✓ Dual/Tri band GSM
- ✓ Right-angled or straight connector
- ✓ Ideal for GSM Telemetry applications



Specifications

Radiating element	Wire
Frequency range	900, 1800, 1900 MHz
Peak gain	1.0 dBi
Polarisation	Linear
Return Loss	-7.0 dB
Power rating	10W
Cable / Connector	SMA Male - straight/right-angle, FME-Female right-angle
Dimensions	Sleeve 45 x 8mm (height x diameter) plus connector

Ordering Options

FTA35011-SM-RA	Targan with right angled SMA-Male connector
FTA35011-SM-ST	Targan with straight SMA-Male connector
FTA35011-FM-RA	Targan with right angled FME-Female connector

Specifications subject to change without notice