

FEATURES

- Available in uncoated and polyester coated stainless steel
- High tensile strength
- Self-locking design
- Suitable for both indoors and outdoors
- excellent resistance to high temperature, chemicals, weather and abrasion
- Can be tightened by hand or tool

RS PRO Steel Stainless Steel Roller Ball Cable Tie, 520mm x 12mm

RS Stock No.: 123-5030



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



Product Description

These RS PRO stainless steel cable ties are an ideal alternative where Nylon 66 cable ties are not suitable such as harsh environments or places where there is heat. These cable ties have a roller ball design which is self-locking and fast and easy to install. Roller ball ties have a locking ball bearing which grips the tie strap and locks the tie as it is tensioned.

General Specifications

Туре	Roller Ball
Colour	Steel
Material	Stainless Steel
Application	Oil and gas, Marine, Chemical, Maintenance, Automotive
Minimum Operating Temperature	-80°C
Maximum Operating Temperature	538°C
Fire Behaviour	Flame Retardant

Mechanical Specifications

Length	520mm
Width	12mm
Tensile Strength	2225N
Maximum Bundle Strength	152mm

Approvals

Standards Met	IEC 62275 (2006), UL-1565, ABS, DNV, Lloyd's, UL



