

# VALUE Cable USB 2.0, C-C, M/M, 60W, white, 2 m

**Product No.** 11.99.8341  
**Manufacturer** VALUE  
**Manufacturer No.** 11.99.8341  
**EAN (single piece)** 7630049632820



**High-quality USB charging cable for smartphones and tablets with improved shielding and the reversible USB-C plug at both ends. Cable sheath made of white textile braiding to match the design of the Apple iPhone 15 products.**

- High quality USB 2.0 cable with improved shielding
- With the reversible Type C connectors at both ends
- Gold-plated contacts for low wear at high plugging cycles
- Suitable for data transfer rates of up to 480 Mbit/s
- Supports USB Power Delivery to 20V / 3A

| Technical specifications |                                                   |
|--------------------------|---------------------------------------------------|
| Manufacturer             | VALUE                                             |
| Product group            | Cable                                             |
| Product type             | USB 2.0 Cable                                     |
| Colour                   | white                                             |
| Length                   | 2 m                                               |
| Transfer quality         | USB 2.0 Hi-Speed 480 Mbit/s                       |
| Connection ports         | USB Type C (USB-C) Male / USB Type C (USB-C) Male |
| Side 1 Connector Type    | USB Type C (USB-C)                                |
| Side 1 Connector Gender  | Male                                              |

|                                    |                    |
|------------------------------------|--------------------|
| Side 2 Connector Type              | USB Type C (USB-C) |
| Side 2 Connector Gender            | Male               |
| Colour (Cable)                     | White              |
| Maximum data transfer rate         | 480 Mbit/s         |
| Area of application                | External           |
| Power (max.)                       | 60 W               |
| Cable shielding                    | Screened           |
| Operating temperature min.         | 0 °C               |
| Operating temperature max.         | 45 °C              |
| Storage temperature min.           | -20 °C             |
| Storage temperature max.           | 70 °C              |
| Weight                             | 50.5 g             |
| Height of packaging (single piece) | 20 mm              |
| Width of packaging (single piece)  | 100 mm             |
| Depth of packaging (single piece)  | 100 mm             |
| Package weight (single piece)      | 0.063 kg           |