








— FITS .250 SERIES
FASTON TAB
VIEW A-A

1— DIM'S IN BRACKETS ARE IN INCHES.
2— CONTINUOUS STRIP ON REELS.



SECT B-B



SECT C-C

METRIC

3.05—4.32 [.120—.170] DIA	0.8—2.0mm ² [18—14] AWG	0.81 ^{±0.025} [.032] [.001]	41202
INSUL RANGE	WIRE SIZE	MATING TAB THK	PART NO

0	4.57 [.180]	6.4 [.252]	F	3.05 [.120]	1.90 [.075] 1.68 [.066] 1.55 [.06]	2.0mm ² [14] 1.3mm ² [16] 0.8mm ² [18]
TYPE INSUL BARREL CRIMP	WIDTH	STRIP LENGTH ±0.38 [±.015]	TYPE WIRE BARREL CRIMP	WIDTH	±.051[±.002] HEIGHT	WIRE

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 2/7/86	TE Connectivity			
DIMENSIONS: MM		CHK G YETTER 2/7/86				
		APVD C MEYERS 2/7/86	NAME RECEPTACLE, FASTON, 6.35 [.250] SERIES			
		PRODUCT SPEC				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC				
MATERIAL BRASS 0.46 [.018]		FINISH —	WEIGHT —	SIZE A3	CAGE CODE 00779	DRAWING NO C-41202
CUSTOMER DRAWING			RESTRICTED TO —	SCALE NTS	SHEET 1 OF 1	REV U1