



6300

Single-Row Deep Groove Ball Bearings



Boundary Dimensions

d	10	mm	Bore diameter
D	35	mm	Outside diameter
B	11	mm	Width
r (min.)	0.6	mm	Chamfer dimension

Basic Load Ratings

Cr	8900	N	Basic dynamic load rating
C0r	3450	N	Basic static load rating

Speeds

Grease	26000	min-1	Grease lubrication
Oil (Oil-bath)	30000	min-1	Oil-bath lubrication

Abutment and Fillet Dimensions

da (min.)	14	mm	Diameter of shaft abutment
da (max.)	16.5	mm	Diameter of shaft abutment
Da (max.)	31	mm	Diameter of housing abutment
ra (max.)	0.6	mm	Radius of shaft or housing fillet

Calculation factors

fo	11.2		Factor
----	------	--	--------

Additional information

z	6		Number of Balls
Dw	7.144	mm	Ball Diameter

Mass

Mass approx.	0.052	kg	Mass approx.
--------------	-------	----	--------------

