

Previously known as: Hycron® 27-905



Oil



Heavy Duty

Heavy-duty work gloves, delivering robust grip and comfortable hand protection

- **Strengthened grip:** Combining ANSELL GRIP™ and RIPEL™ Technology, ActivArm® Hycron® 27-905 work gloves offer superb grip and liquid repellence, fending off oils, lubricants and chemical hazards in dry, wet or oily conditions
- **Advanced durability:** These protective gloves' FORTIX™ Technology nitrile coating ensures highly advanced abrasion resistance, for truly durable hand protection
- **Added comfort:** ActivArm® Hycron® 27-905 safety gloves grant wearers a cool feeling and better perspiration relief thanks to a soft polycotton liner
- **Certified antistatic capabilities:** These silicone-free industrial gloves comply with EN 1149 standards, ensuring product integrity



Industries

- Automotive
- Machinery and Equipment
- Metal fabrication
- Construction
- Mining
- Oil and gas

Applications

- Garbage collection & sorting
- Handling abrasive materials
- Handling dry, wet or oily large objects
- Maintenance
- Primary assembly



27-905

Tougher oil repellent glove with ANSELL GRIP™ Technology

Previously known as: Hycron® 27-905

Key Features

- **ANSELL GRIP™ Technology:** More grip, less force, higher output
- **Flexible nitrile coating:** For highly durable abrasion-resistant gloves
- **Soft polycotton liner:** Less perspiration, for a cool, comfortable feel

Performance Standards & Regulatory Compliance



Technologies



Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
ActivArm® Hycron® 27-905	Finishing: Fully Coated Coating Material: Nitrile Liner Material: Polycotton Cuff Style: Safety Cuff		8, 9, 10, 11	265-295 mm; 10.43-11.61 inches	Blue	12 pairs/bag, 6 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Australia

Ansell Limited
Level 3,678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

