





SPECIFICATION
 MATERIAL
 Insulator: Polyester Resin And Glass Fiber
 Reinforced (UL94V-0)
 Contacts: Brass or Phosphor Bronze
 CONTACT PLATING: 1u"~30u" Selective Gold Over Nickel



Plastic strain relief

Stainless steel strain relief

POSITION	A±0.13	B±0.25	C±0.25	D±0.13	E ₀ ^{+0.40}	F±0.25	G±0.25
09	24.99	30.80	11.08	8.31	16.3	18.60	16.92
15	33.32	39.10	19.39	16.62	24.2	26.60	25.25
25	47.04	53.09	33.24	30.47	38.6	40.90	38.96
37	63.50	69.40	49.86	47.09	54.8	57.10	55.45

UNLESS OTHERWISE SPECIFIED TOLERANCE		
ANG.	±5°	
0.	±0.5	
.0	±0.3	
.00	±0.2	
SCALE: AS SHOWN	UNIT: mm	
DRAWN		DRAWN NAME:
CHECKED	/ /	I.D.C. D-SUBMINIATURE CONNECTORS
APPROVED	/ /	PRODUCT NO. 4096409
REV.		FILE NAME: 4096409

REV.	DESCRIPTION	DATE	SIZE	REV.
			A4	