

# Endress+Hauser Pressure sensor PMC11-AA1L1PBWWJA

Compact gauge pressure transducer with capacitive, oil-free ceramic sensor.



Picture for reference only. Product appearance may vary based on configuration

The Cerabar PMC11 is a very compact pressure transmitter with capacitive, oil-free ceramic sensor that can measure gauge pressure from 400mbar up to 40bar ( depending on configuration) in gases, vapors, liquids and dust. The PMC11 is designed for standard applications in the process industry.

- Easy usability
- High performance
- Long term stability
- High material quality

### Configuration of PMC11-AA1L1PBWWJA:

|                        |     |                                                         |
|------------------------|-----|---------------------------------------------------------|
| Approval:              | AA  | Non-hazardous area                                      |
| Output:                | 1   | 4-20mA                                                  |
| Electrical Connection: | L   | Plug M12, IP65 NEMA Type 4X Encl.                       |
| Sensor Range:          | 1P  | 10bar/1MPa/150psi gauge, overload:<br>40bar/4MPa/600psi |
| Calibration; Unit:     | B   | Sensor range; mbar/bar                                  |
| Process Connection:    | WWJ | Thread ISO228 G1/2, hole 11.4mm, 316L                   |
| Seal:                  | A   | FKM                                                     |

Alternative part number: PMC11-1369/0