SIEMENS

Data sheet 8MF1008-2UB51-2

SIVACON, base, with side cable entry, T: 800 mm, W: 1000 mm, zinc-plated



Model	
product brand name	SIVACON
design of the product	With lateral cable entry
design of the surface	zinc plated
design of the product EMC version	No
material	steel
product component	
• ventilation	No

Mechanical Design	
width	1 000 mm
depth	800 mm
net weight	12 000 g

Approvals Certificates

General Product Approval	Test Certificates	other	
	Special Test Certific-ate	Confirmation	Miscellaneous

other	Environment	
Miscellaneous	Siemens EcoTech	Environmental Con-firmations

Further information

Information on the packaging
https://support.industry.siemens.com/cs/ww/en/view/109813875
Information- and Downloadcenter (Catalogs, Brochures,…)
http://www.siemens.com/lowvoltage/catalogs
Industry Mall (Online ordering system)
https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8MF1008-2UB51-2
Service&Support (Manuals, Certificates, Characteristics, FAQs,...)
https://support.industry.siemens.com/cs/ww/en/ps/8MF1008-2UB51-2
Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)
http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8MF1008-2UB51-2
CAx-Online-Generator
http://www.siemens.com/cax
Tender specifications
http://www.siemens.com/specifications

Subject to change without notice
© Copyright Siemens



last modified: 6/3/2024

Subject to change without notice
© Copyright Siemens

Subject to change without notice
© Copyright Siemens