



OPEN END SLOGGING WRENCH METRIC 70MM

- Designed for extra heavy duty work
- For use with a hammer or sledge hammer
- Manufactured in impact resistant Chrome molybdenum
- Designed and manufactured to DIN 133

Open End Slogging Wrench 70mm

General information

Country of origin: Taiwan
Barcode: 5020385124523
Tarriff code Europe: 8204110000
ECCN US: EAR99
ETIM: EC002188
UNSPSC: 27111706

Dimensions

Net weight (g): 4300
Height (mm): 22
Length: 367 mm

Attributes

Product type: Slogging Wrenches
Material: Cr-Mo
Certificates: N/A
Size: 70 mm
Tethering facility: No
Jaw diameter: 148.9
Jaw height (mm): 36.0
Offset angle jaw (°): 15



DESIGNED IN SWEDEN

TengTools is a Swedish company present in more than 30 markets worldwide, and offers hand tools in smart storage solutions for demanding professionals within the automotive, maintenance and engineering sectors, as well as motor sport enthusiasts who aspire to use the same tools as top mechanics across the globe.



Sandbergsvägen 3
441 39 Alingsås, Sweden