

## **FSD-3; Attention: Discontinued item. 1x switching output flow (PNP) + 4...20 mA flow @ 15...35 V DC**

### **Electronic Flow Switch with Display**

Item number: 14174699

Quantity: 1 pcs.

Order code: FSD-3-P1Z-SZ-2NDZ-M4ZW-ZZZ-Z 2 W1011FSD-S2R2HO S-GSES

Overview: FSD-3; Attention: Discontinued item. 1x switching output flow (PNP) + 4...20 mA flow @ 15...35 V DC

Probe length: 30 mm; 1/2 NPT ;

Configuration flow switch: Factory setting acc. to manual circular connector M12x1, 4-pin; U+=1, U-=3, S+=2, SP1=4

Specifications according to data sheet: FL 80.01

Details: Electronic Flow Switch with Display

Model FSD-3

Specifications according to data sheet: FL 80.01

Attention: Discontinued item.

Output signal 1: 1x switching output flow (PNP)

Output signal 2: 4...20 mA flow

Measuring Range Flow: Standard

Probe length: 30 mm

Process connection: 1/2 NPT

Configuration flow switch: Factory setting acc. to manual

Power supply: 15...35 V DC

Electrical connection: circular connector M12x1, 4-pin

Pin assignment: U+=1, U-=3, S+=2, SP1=4

Permissible medium temperature: -20...+85°C

Test protocol: without test protocol

Measuring Range Temperature: without