



差込口が斜めで差し込みやすく、個別スイッチが付いた節電対策に役立つタップ。2P・6個口・1m・ホワイト。

TAP-S30-1W

節電タップ（2P・6個口・1m・ホワイト）

JANコード 4969887829639



仕様

コード色	ホワイト
定格容量	15A・125V（1500Wまで）
差し込み口形状	2P
プラグ	2P（絶縁キャップ付きスイングプラグ）
差込口	2P・6個口（ノーマルタイプ）
差込口間隔	36mm 一番端の差込口のみ52mm
シャッター	あり
マグネット	あり
雷ガード	あり
コード導体サイズ	VFF1.8スケア（SQ）2心
コード仕上り外形寸法	4.2mm×7.6mm
電源コード長	1m
制限電圧	395V
サージ耐量	2500A
バリスタ電圧	240V
スイッチ	一括集中スイッチ、個別スイッチ
コードの種類	二重被ふくコード
サイズ	W300×D46×H32mm
重量	約340g

認証	電気用品安全法（PSE）技術基準適合品
使用地域	日本国内のみ。日本以外ではご使用いただけません。

特長

- 個別スイッチにより、機器ごとのON・OFFが可能のため、必要でない機器をこまめにOFFすることで待機電力を減らし、節電や節約効果に役立ちます。
- ホコリ防止シャッターを採用しているため、使用しないコンセントへのホコリなどの侵入を防ぎ、火災などの事故予防にもなります。
- 1番端にある差込口は間隔を52mm空けているため、ACアダプタなども無理なく差し込めます。
- 二重被覆コードを採用しており、より丈夫で安全なコードとなっています。
- トラッキング防止予防に効果的な絶縁キャップ付きのスイング式プラグを採用しており、スッキリとした配線が可能です。
- 底面には強力マグネットのネオジムを装着しており、デスクのスチール製フレームなどにしっかり貼り付けられます。
- 一括集中スイッチ付き、雷ガード付きタイプです。

This power strip features angled outlets for easy insertion and individual switches for energy conservation. 2-pin, 6 outlets, 1m, white.
TAP-S30-1W

Specifications

- Cord Color : White
- Rated Capacity : 15A, 125V (up to 1500W)
- Outlet Type : 2P
- Plug : 2P (Swing Plug with Insulation Cap)
- Outlet Type : 2P, 6 Outlets (Standard Type)
- Outlet Spacing : 36mm
52mm for the Endmost Outlet Only
- Shutter : Yes
- Magnet : Yes
- Lightning Protection : Yes
- Cord Conductor Size : VFF1.8 SQ (Single-Core) 2-Core
- Finished Cord Dimensions : 4.2mm x 7.6mm
- Power Cord Length : 1m
- Limiting Voltage : 395V
- Surge Withstand : 2500A
- Varistor Voltage : 240V
- Switch : Centralized Switch, Individual Switch
- Cord Type : Double-Insulated Cord
- Dimensions : W300 x D46 x H32mm
- Weight : Approx. 340g
- Certification : Compliant with the technical standards of the Electrical Appliance and Material Safety Act (PSE)
- Use : Japan only. Cannot be used outside of Japan.

Features

- Individual switches allow you to turn devices on and off individually, allowing you to frequently turn off unnecessary devices, reducing standby power consumption and contributing to energy conservation and cost savings.
- Dust-proof shutters prevent dust and other particles from entering unused outlets, helping to prevent fires and other accidents.
- The sockets at the very end are spaced 52mm apart, making it easy to plug in AC adapters and other devices.
- The double-insulated cord provides a stronger and safer cord.
- The swing-type plug with an insulating cap effectively prevents tracking, allowing for neat wiring.
- A powerful neodymium magnet is attached to the base, allowing it to be firmly attached to the steel frame of a desk.
- Includes a centralized switch and lightning protection.