



PRODUCT-DETAILS

HAAM0304G1

1/2NPT NICKEL FLAMEPROOF FOR 16MM C



概要信息	
产品型号	HAAM0304G1
产品ID	7TCA297090R0062
欧洲商品编号(EAN)	5011949016866
目录说明	1/2NPT NICKEL FLAMEPROOF FOR 16MM C
详细描述	Liquid Tight Fitting for Conduit, ATEX Flameproof G1 Gland, Straight with External Male Thread, Conduit Size 16mm, 1/2 Inch NPT Thread, CSA, Group I & II, Zones 1, 2, 21 and 22, Class I Div2 ABCD, Class II Div1 EFG, Nickel Plated Brass with Epoxy Resin Barrier

其他信息	
应用	Ideal for Ex I & II 2 GD Gas and Dust, Exde IIC and Exe II Applications
产品应用类型	Liquid Tight Conduit Fitting with Flameproof Barrier

订货信息	
欧洲商品编号(EAN)	5011949016866
UPC	786210243078

技术参数	
Number of Batteries	0
颜色	Metallic
材料	Brass with Epoxy Resin Barrier
尺寸	Conduit Size 16mm ; 1/2 Inch NPT Thread

环境条件	
WEEE 类别	Product Not in WEEE Scope

包装信息	
1级包装单元	1 piece
1级包装高度	7.87 in 200 mm
1级包装长度	1 in 25 mm
1级包装宽度	5.9 in 150 mm

认证及声明（文件编码）	
数据手册，技术资料	HAAM0304G1
说明书和手册	HAAM0304G1
符合性声明 - CE	9AKK107492A9617
RoHS信息	9AKK107992A8994
RoHS日期	9AKK107992A8994
REACH Declaration	9AKK107992A8994

分类	
ETIM 8	EC001180 - Screw connection for protective metallic hose
UNSPSC	39121420

分类	
低压产品及系统 → 安装产品 → 电缆保护、防爆和照明 → Flexible Cable Protection Systems	

