




Connectors > PCB Connectors > Wire-to-Board Connectors > FFC, FPC & Ribbon Connectors > Ribbon Connector Accessories >

Female Socket Connectors: Strain Relief



Flat Flexible Cable Accessory Type: **Strain Relief**

Number of Positions: **14**

[All Female Socket Connectors: Strain Relief \(14\)](#)

Features

Product Type Features

Flat Flexible Cable Accessory Type	Strain Relief
------------------------------------	---------------

Configuration Features

Number of Positions	14
---------------------	----

Body Features

Primary Product Material	Glass-Filled Thermoplastic
Primary Product Color	Blue

Dimensions

Product Length	22.45 mm
----------------	----------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Quantity	50
Packaging Method	Package

Other

Comment	Female Socket Connector
---------	-------------------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)






EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability









Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # CAT-AM74-UN384H AMP-LATCH UNIVERSAL HEADERS	 TE Part # 2-1761603-5 IDC LOW PRO HDR 14P VERT BLUE	 TE Part # 5103309-2 A/L LOW PRO HDR 14P VERT BLACK	 TE Part # 5103310-2 A/L LOW PRO HDR 14P RA BLACK
 TE Part # 1761607-5 IDC LOW PRO HDR 14P RA LG LAT BLK	 TE Part # 1-111446-5 14 UNIV I/O, NO EARS, LEAD FREE	 TE Part # 2-1761606-5 IDC LOW PRO HDR 14P VERT LG LA	 TE Part # 5103308-2 A/L LOW PRO HDR 14P VERT BLACK



 TE Part # 2-1761607-5 IDC LOW PRO HDR 14P RA LG LAT	 TE Part # 5103311-2 A/L LOW PRO HDR 14P RA BLACK	 TE Part # 5104338-2 A/L LOW PRO HDR 14P VERT HT	 TE Part # 1-111504-5 014 UNIV I/O 30DP NO EARS LTCH
 TE Part # 1761681-5 IDC LOW PRO HDR 14P VERT HT BLACK	 TE Part # 2-1761605-5 IDC LOW PRO HDR 14P RA BLUE	 TE Part # 1761682-5 IDC LOW PRO HDR 14P RA HT BLACK	 TE Part # 1761686-5 IDC LOW PRO HDR 14P VERT LG LAT
 TE Part # 2-1761679-5 IDC LOW PRO HDR 14P VERT BLUE	 TE Part # 1761606-5 IDC LOW PRO HDR 14P VERT LG LA	 TE Part # 1658526-8 609-1430LF FEM SOCKET, LEAD FREE	 TE Part # 2-1761680-5 IDC LOW PRO HDR 14P RA BLUE

Documents

Product Drawings

609-1431HD=FSKT IDC S 14 SR

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_5-1437020-1_C.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_5-1437020-1_C.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_5-1437020-1_C.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



Ribbon Cable Interconnect Solutions

English