



# Datasheet

## RS Wall Volume Controller, 100W

ENGLISH

RS Stock 406-0905



### Specification:

Characteristics	
Line voltage	100V
Power rating	100W
Switch positions	11 + off
Attenuation per step	3dB*
Total attenuation	36dB
Insertion loss	Less than 0.5dB
Relay spec	Coil 24V DC 22mA, contact rating 10A
Plate size	Double gang
Dimensions (H x W x D)	24 x 116 x59.6