

BL2 BPC 1541S-4/64 - Box PC

1272827

<https://www.phoenixcontact.com/in/products/1272827>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



IP30-rated fanless industrial box PC (BPC) with energy-efficient Intel® Atom® E3940 processor with 64 GB eMMC

Commercial data

Item number	1272827
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	*****
Product key	DRBABA
GTIN	4063151464257
Weight per piece (including packing)	75 g
Weight per piece (excluding packing)	62 g
Customs tariff number	84715000
Country of origin	TW

BL2 BPC 1541S-4/64 - Box PC

1272827

<https://www.phoenixcontact.com/in/products/1272827>



Technical data

Notes

Note on application

Note on application	Only for industrial use
---------------------	-------------------------

Product properties

Product type	Box PC
--------------	--------

Computer data

Processor	Intel® Atom™ E3940 1.6 GHz
Operating system	without operating system
RAM	4 GB LPDDR4
Data storage system	eMMC internal, 64 GB
Cooling	passive

Display

Display type	none
--------------	------

System properties

User software	without user software
---------------	-----------------------

Electrical properties

Maximum power dissipation for nominal condition	16.8 W
---	--------

Supply

Supply voltage (DC)	24 V DC $\pm$ 20% (CE rating)
Supply voltage range	12 V DC ... 30 V DC (Labeled operational voltage is 12 ... 30 V DC)
Max. current consumption	0.7 A (24 V DC)
Typical current consumption	0.53 A (24 V DC)

Connection data

Power supply

Connection method	Screw connection
Conductor cross section, rigid	0.14 mm ² ... 1.5 mm ²
Conductor cross section, flexible	0.14 mm ² ... 1.5 mm ²
Conductor cross section AWG	28 ... 16
Stripping length	7 mm

Interfaces

Interfaces	1x DP++
	2x USB 3.0
Network	2x Ethernet (10/100/1000 Mbps), RJ45
LAN chipset	Intel® I210-AT

BL2 BPC 1541S-4/64 - Box PC



1272827

<https://www.phoenixcontact.com/in/products/1272827>

Dimensions

External dimensions

Width / Height / Depth	99 mm / 92 mm / 46 mm
------------------------	-----------------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP30
Ambient temperature (operation)	-40 °C ... 70 °C (With 0.5 m/s airflow. NOTE: Operation above 60°C ambient temperature invalidates the UL listing.)
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Permissible humidity (operation)	5 % ... 85 % (non-condensing)
Shock	15g, 11 ms in accordance with IEC 60068-2-27
Vibration (operation)	1g, according to EN 60068-2-6

Approvals

Conformity/Approvals

Conformance	CE-compliant
-------------	--------------

Mounting

Mounting type	DIN rail mounting
	Panel mounting (Accessories required)

BL2 BPC 1541S-4/64 - Box PC



1272827

<https://www.phoenixcontact.com/in/products/1272827>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/in/products/1272827>



EAC-RoHS
Approval ID: RU*-DE*HB.B.00386/20



IECEE CB Scheme
Approval ID: US-39601-M1-UL



UL Listed
Approval ID: E238705 D12:D1050



cUL Listed
Approval ID: E238705 D12:D1050

cULus Listed

BL2 BPC 1541S-4/64 - Box PC



1272827

<https://www.phoenixcontact.com/in/products/1272827>

Classifications

ECLASS

ECLASS-11.0	19200102
ECLASS-12.0	19200102
ECLASS-13.0	19200102

ETIM

ETIM 9.0	EC001413
----------	----------

UNSPSC

UNSPSC 21.0	43211500
-------------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-15
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

BL2 BPC 1541S-4/64 - Box PC



1272827

<https://www.phoenixcontact.com/in/products/1272827>

Accessories

SI-RND-U1A - Data interface

1425185

<https://www.phoenixcontact.com/in/products/1425185>

Service socket with USB A 3.0 (socket/socket), with protective cover



DP TO VGA ADPTR - Adapter

2400173

<https://www.phoenixcontact.com/in/products/2400173>

DisplayPort to VGA video adapter



BL2 BPC 1541S-4/64 - Box PC

1272827

<https://www.phoenixcontact.com/in/products/1272827>



DP TO DVI ADPTR - Adapter

2400174

<https://www.phoenixcontact.com/in/products/2400174>

DisplayPort to DVI-i video adapter



VL 2.0M DP CABLE - Connecting cable

2404774

<https://www.phoenixcontact.com/in/products/2404774>

DisplayPort (DP) cable (2 m) for use with industrial computers



BL2 BPC 1541S-4/64 - Box PC

1272827

<https://www.phoenixcontact.com/in/products/1272827>



BL2 BPC 1500 WALL MOUNT KIT - Mounting kit

1147655

<https://www.phoenixcontact.com/in/products/1147655>

Mounting kit



BL2 BPC 1500 RTC BATTERY - Battery/accumulator

1147739

<https://www.phoenixcontact.com/in/products/1147739>

Replacement battery (BR2032) for BL2 BPC 1500... IPCs



BL2 BPC 1541S-4/64 - Box PC

1272827

<https://www.phoenixcontact.com/in/products/1272827>



BL2 BPC 1500 DIN RAIL KIT - Mounting kit

1147464

<https://www.phoenixcontact.com/in/products/1147464>



DIN rail mounting kit for BL2 BPC 15... products

BL2 BPC 1500 64GB M.2 SSD KIT - Memory

1147738

<https://www.phoenixcontact.com/in/products/1147738>



64 GB M.2 SSD kit for BL2 1500 IPC, heat spreader, bracket, and thermal pads are included

BL2 BPC 1541S-4/64 - Box PC

1272827

<https://www.phoenixcontact.com/in/products/1272827>



BL2 BPC 1500 128GB M.2 SSD KIT - Memory

1147737

<https://www.phoenixcontact.com/in/products/1147737>

128 GB M.2 SSD kit for BL2 1500 IPC, heat spreader, bracket, and thermal pads are included



MC 1,5/ 2-STF-3,5 - PCB connector

1847055

<https://www.phoenixcontact.com/in/products/1847055>



PCB connector, nominal cross section: 1.5 mm², color: green, nominal current: 8 A, rated voltage (III/2): 160 V, contact surface: Sn, contact connection type: Socket, number of potentials: 2, number of rows: 1, number of positions: 2, number of connections: 2, product range: MC 1,5/-STF, pitch: 3.5 mm, connection method: Screw connection with tension sleeve, screw head form: L Slotted, conductor/PCB connection direction: 0 °, plug-in system: COMBICON MC 1,5, locking: Screw locking mechanism, mounting method: Screw flange, type of packaging: packed in cardboard

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.

A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420

info@phoenixcontact.co.in