

FEATURES

- Cable assembling
- Under floor wiring
- Cable management and tidying
- Great protection for wiring looms and harnesses
- Enclosing fiberoptics
- Fast protection on loose cables

RS PRO Plastic Flexible, Split Conduit Black 25mm x 10m

RS Stock No.: 755-9026



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



Product Description

Introducing the RS Pro range of flexible split conduit, created and designed for the protection and structure of running electrical wiring through machinery or buildings. Split conduit is a strategic choice for users who are looking to enclose cables in a tidy fashion or needing to repair damaged conduit.

General Specifications

Conduit Type	Flexible, Split
Material	Plastic
Colour	Black

Mechanical Specifications

Nominal Diameter	25mm
Outer Diameter	25.8mm
Interior Diameter	21.2mm
Length	10mm

Operation Environment Specifications

Maximum Operating Temperature	+80°C
Minimum Operating Temperature	-20°C


Approvals

Compliance/Certifications	2011/65/EU and 2015/863
Standards Met	RoHS Compliant









Dimensions - mm

RS Item No.	ΑФ	ВФ	С	Packing
7559013	10.7±0.4	16.0±0.4	3.3	25 M / Roll / Bag
7559017	15.0±0.4	19.5±0.4	3.5	25 M / Roll / Bag
7559026	21.2±0.4	25.8±0.4	3.1	10 M / Roll / Bag
7559029	24.3±0.4	32.0±0.4	3.61	10 M / Roll / Bag