



314-PP5

E0812740

PIGTAIL CONNECTOR FOR 2 OR 3 WIRE ENDS, 0.5-1.5mm2, MOISTURE RESISTANT, SELF STRIPPING



Product Properties:

Model	Single-conductor connector
Colour insulation	Blue
Grease filling against corrosion	Yes
Max. number of cores	3 .
Temperature	-40-105 °C
Interrupt free shifting	No
Material insulation	Polyamide (PA)

Dimensions:

Core diameter	0.8-1.4 mm
Max. outer diameter	1.2-3.9 mm
MOQ	1 .
Unit	pck
Nominal cross section	0.5-1.5 mm²

Approvals:

With approval according to UL	Yes
-------------------------------	-----

Compliance:

CA Proposition 65	No CA Prop65
Conflict Minerals	Contain "Tin"
REACH	No SVHC (Latest. 05 Nov 2025)
RoHS	RoHS 3 (2015/863)

SCIP	Not Applicable
US TSCA	No (5 PBT Subs, Feb 2021)

Other information:

ETIM-Class	EC000306 - Low current connector
ETIM-Release	9.0
Trademark	NECORE
Product Group	IDC connector
Search Description	GKK2023 ENR2023V
Alternative SKU	314-PP5
E-no	E0812740

Logistic information:

Barcode	733117614948
Country of origin	US
E-no	E0812740
Item status	Stock item, normally in stock with reservation for in between sales.
MOQ	1 .
Stock code	314-PP5
Taric code	85369010
Unit	pck

*We reserve the right to make technical changes and disclaim any typographical errors.