

PRODUCT-DETAILS

## AMD112153-SB

AMD112153-SB - Switch 3-gang, 2-way, SP 16AX, Triple rocker size - SB



### General Information

Extended Product Type	AMD112153-SB
Product ID	2CLA630210N1556
EAN	8427238101477
Catalog Description	AMD112153-SB - Switch 3-gang, 2-way, SP 16AX, Triple rocker size - SB
Long Description	Rated voltage: 250Vac Rated power: 16AX

### Ordering

EAN	8427238101477
Customs Tariff Number	85365080
Minimum Order Quantity	10 piece

### Dimensions

Product Net Depth / Length	0.122 m
Product Net Height	0.091 m
Product Net Width	0.116 m
Product Net Weight	0.07 kg

### Container Information

Package Level 1 Units	10 piece
Package Level 1 EAN	8427238101477
Package Level 1 Depth / Length	0.122 m
Package Level 1 Height	0.091 m
Package Level 1 Width	0.116 m
Package Level 1 Gross Weight	0.7 kg

## Technical

Ambient Air Temperature	Operation -5 ... +35 °C Storage -5 ... +35 °C
Degree of Protection	IP20
Mounting Type	Flush mounted (plaster)

## Certificates and Declarations (Document Number)

Data Sheet, Technical Information	9AKK106930A7740
Instructions and Manuals	9AKK106930A7740
Declaration of Conformity - CE	No declaration needed

## Classifications

ETIM 5	EC001590 - Switch
ETIM 6	EC001590 - Switch
ETIM 7	EC001590 - Switch
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

## Categories

Low Voltage Products and Systems → Switch Assortments → Flush Mounted Range BS - Niessen → Design Millenium → Flush Mounted Inserts with Cover Plate → Mechanical Switch / Push Button

Low Voltage Products and Systems → Switch Assortments → Light / LoadControl → Mechanical Switch / Push Button → Mechanical Switch / Push Button - Flush Mounted → Mechanical Switch / Push Button

