

Datasheet

RS Pro Stainless Steel Drop-In Anchor M8, fixing hole diameter 10mm, length 30mm

RS Stock No: **622-2177**



Product Details

RS Pro stainless steel drop-in anchor with M8 threading size, is compatible with concrete with a compressive strength greater than 20 N/mm². This anchor measures 30 mm long and is suitable for 10 mm fixing hole diameter.

Features and Benefits

- A deformation controlled anchor system
- Suitable for use in concrete
- Compressive strength greater than 20N/mm²
- 10 mm fixing hole diameter
- 30 mm long



Specifications:

Material	Stainless Steel
Type	Drop In Anchor
Fixing Hole Diameter	10 mm
Length	30 mm
Thread Size	M8
Grade	316 (A4)
Internal Thread Length	13 mm
Minimum Hole Depth	30 mm