



## BLACKWIRE 310/320

Economically designed for  
enterprise wide deployment

High quality headsets ideal for large  
unified communication deployments.

Simplicity meets durability

# BLACKWIRE 310/320

## BLACKWIRE 320 (stereo)



- A Durable, metal headband
- B Foam ear cushions
- C Noise-cancelling microphone
- D Call answer/end, mute, volume +/-
- E USB connection

## BLACKWIRE 310 (monaural)



### TOP NOTCH FEATURES. BOTTOM LINE PERFORMANCE.

Enter UC with the best-featured headset you never thought your budget could afford. Blackwire 300 Series USB headsets are a simple-to-use, comfortable, and durable choice for conference calls, Web-based training, and PC multimedia applications. Plus, they're priced right, easy to deploy, and offer a simple-to-upgrade UC solution that IT can roll out easily and rely on.

### SIMPLICITY MEETS DURABLE DESIGN

- Two wearing styles available: hi-fi stereo (320) or monaural (310) design, featuring basic foam ear cushions.
- Lightweight metal headband offers durability and a customisable, comfortable fit
- Intuitive inline controls to answer/end calls, control volume, and mute
- Smartly placed indicator lights and helpful audio alerts give user call, mute, and volume status

### OUTSTANDING AUDIO QUALITY

- Wideband audio with noise-cancelling for high-quality PC telephony
- Dynamic EQ feature automatically adjusts audio for voice or multimedia use
- Noise-cancelling microphone filters out background sound
- Enhanced Digital Signal Processing (DSP) provides more natural voice sound
- SoundGuard® technology provides protection against audio spikes

### ADDITIONAL INFORMATION

|                    |  |
|--------------------|--|
| Connects to        | PC via USB, compatible with Windows® or Mac OS   |
| Ideal for          | Users transitioning to PC telephony for webinars, conference calls, music, and other multimedia applications   |
| Audio performance  | Dynamic EQ, microphone frequency response 100 Hz–10 kHz optimal for wideband voice telephony (up to 6,800 Hz), hi-fi stereo (C320) output from 20 Hz–20 kHz, enhanced digital signal processing (DSP), noise-cancelling microphone |
| Hearing protection | SoundGuard: Acoustic limiting for protection against sounds above 118 dBA  |
| Weight             | Monaural: 86g / Binaural: 114g   |
| Guarantee          | 2 years  |

| Model             | Description  | Part number |
|-------------------|--|-------------|
| C310 (monaural)   | UC standard version built for UC applications and          | 85618-02    |
| C320 (binaural)   | softphones from Avaya®, Cisco®, IBM®, Skype™ and more*     | 85619-02    |
| C310-M (monaural) | Version Certified for Skype for Business and Optimized for | 85618-01    |
| C320-M (binaural) | Microsoft® Lync®   | 85619-01    |

\* Download the latest release of Plantronics Spokes™ software to get one-touch call answer/end with these softphones.

For more information about the Blackwire 310/320 or any other Plantronics products, please visit our website at [plantronics.com](http://plantronics.com)

### GLOBAL SERVICE AND SUPPORT

Backed by Plantronics industry-leading global service and support.

Plantronics Ltd, Royal Wootton Bassett, UK, 0800 410014 or +44 (0)1793 842200

Connect with Plantronics   