

Indicator element

84-8001.2320

Distribution by
Rs-online



<https://rs-online.eao.com/component/84-8001.2...>

Your product:



84-8001.2320

Indicator element

OPERATING-/INDICATION PART

Illumination colour: Red

ELECTRICAL CHARACTERISTICS

Operating voltage: 12 V DC $\pm 10\%$

MECHANICAL CHARACTERISTICS

Terminal: Plug-in terminal, 2.8 x 0.8 mm

Weight: 0.006 kg

AMBIENT CONDITION

IP Protection: IP40

CERTIFICATE

REACH: REACH compliant

RoHS: RoHS compliant

OTHER

Short Description: Indicator element, Red, Single-LED, 12 V DC $\pm 10\%$, Plug-in terminal, 2.8 x 0.8 mm

Kind of illumination: Single-LED

Hints: LED and built-in resistor included
Standard version: Cable length 300 mm
Other options on request: Customisation of cable and connectors, rear side fully sealed (IP 67)
Protection degree (rear side): IP 40, upgrade to IP 67 with plug Part No. 84-900 possible. With applications where strong vibrations occur, the plugs may become

loose

Luminosity and wave length variations caused by LED manufacturing processes may cause slight differences regarding the illumination. The customer has to decide what resistor shall be used to the LED

Wiring diagrams:

