



### Main

Range of product	Merten inserts
Product or component type	Switch
Device presentation	Mechanism

### Complementary

Switch function	1-pole 1-way
Actuator	Rocker
Device mounting	Flush
Fixing mode	By screws and claws
[Ue] rated operational voltage	250 V
Rated current	10 AX
Maximum switching current	10 A
Number of rocker	2
Pilot light	Red indicator
Connections - terminals	Screwless terminals
Material	Metal Plastic

### Environment

IP degree of protection	IP20
-------------------------	------

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins