


SPECIFICATIONS	
HOUSING MATERIAL/COLOR	GLASS FILLED NYLON/BLACK
CONTACT MATERIAL/PLATING	BRASS/GOLD
COUPLING NUT MATERIAL/PLATING	DIECAST ZINC/NICKEL
RATED CURRENT [A]	9.0 A
RATED VOLTAGE [V]	250 V
MAXIMUM WIRE SIZE	16 AWG
TERMINATION METHOD	SCREW TERMINAL
TEMPERATURE RATING	-40°C to +90°C (-40°F to +194°F)
PROTECTION CLASS	IP 67



2.

3.


SEE SPECIFICATIONS


30247

ECO NO.

05/10/10

DATE





DESCRIPTION

## SOURCE DRAWING - FOR REFERENCE ONLY RELATED DOCUMENTS 3RD ANGLE PROJECTION THIS DRAWING IS PROPERTY OF TURCK INC. USE OF THIS DOCUMENT 3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 turck inc

WITHOUT WRITTEN PERMISSION IS High Technology Sensors and Automation Controls PROHIBITED. DATE 07/19/07 MATERIAL RDS ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR DSGN SCALE SEE SPECIFICATIONS UNIT OF MEASUREMENT REFERENCE ONLY FINISH CONTACT TURCK FOR MORE

INFORMATION

turck.com B 4151-0/13.5/DNET

1 = 1.0MILLIMETER [ INCH ]

DO NOT SCALE THIS DRAWING

REV

(763) 553-7300

(763) 553-0708 fax

В

SHEET 1 OF 1

IDENTIFICATION NO. U3-01276

FILE: U3-01276