



182.72.104.66HKNadelhülsen

## Drawn cup needle roller bearings with open ends HK4016 (Series HK) to DIN 618/ISO 3245

The datasheet is only an overview of dimensions and basic load ratings of the selected product. Please always observe all the guidelines in these overview pages. Further information is given on many products under the menu item "Description". You can also order comprehensive information via the Catalogue ordering system ([https://www.schaeffler.de/content.schaeffler.de/en/news\\_media/index.jsp](https://www.schaeffler.de/content.schaeffler.de/en/news_media/index.jsp)) or by telephone on +49 (91 32) 82 - 28 97.

Fw	40 mm
D	47 mm
C	16 mm Tolerance: 0/-0,3
rmin	0,8 mm
m	39 g Mass
Cr	20000 N Basic dynamic load rating, radial
Cor	38500 N Basic static load rating, radial
Cur	5000 N Fatigue limit load, radial
ng	6600 1/min Limiting speed
nb	5000 1/min Reference speed
	LR35X40X16,5 Suitable inner ring
	IR35X40X17-XL Suitable inner ring
	SD40X47X4 Suitable sealing ring
	G40X47X4 Suitable sealing ring

