

BLAZE -Specialities rtridge roll/ Pencils
Cartridge roll/ Pencils BLAZE-12.7x38.1x3.175#80

Artical Number: 66261194396

EAN: 3157629493342

Description

The Best choice for hard-to-grind materials, stainless steel, cobalt, inconel and titanium. Used on inside surfaces and corners where other abrasive shapes cannot reach and dressing fillet weld seams on metal structures. Typically these are used on high-speed air grinders and are always mounted on a mandrel. Ideal for flash removal, polishing, or removing machine tool marks, and edge breaking. A compact, lightweight, handheld tool for mandrel-mounted abrasive products that allows for better control than larger die grinders and is a must for any detail work on small parts. Cartridge and Spiral rolls are strips of abrasive cloth rolled and glued to form a solid shape that is designed to break down during use and reveal the next layer of abrasive. Easy to control and to replace due to special mandrel.

Features

Available in straight or tapered shapes

Next-generation Ceramic Alumina abrasive grain

Advanced gridding aid

Improved resin bond system

Strong X-weight cotton backing

Benefits

Straight rolls wear to the shape required

provides greatest productivity with significantly faster cut rates and longer life

for cooler cut and reduces loading and glazing

for exceptional grain retention and longer life

for durability and even wear

Application Data

Material Application:	STEEL
Machine:	Die Grinder
Process:	Sanding
Equipments:	

Technical Data

MarketingCAP:	R920	Length:	38.1 mm
BackingMaterial:	Heavy Cotton X	ArborHole:	3.175 mm
Grit:	80		
Color:	Orange	Glue:	1/2
CoatedShape:	Coated Specialties		
CoatedSubShape:	Cartridge rolls		
		Shape	

Logistic Data

Naked Product Weight	0.007 kg	Packed Product Dimension	156.000 mmx158.000 mmx112.000 mm
Naked Product Dimension	12.7x38.1x3.175	pack Qty (parts per pack)	100 pc
Units per part	1 pc	Packed Product Weight	0.600 kg