

## / SUXXEED OFFROAD BLACK S3 High/ 67203 / EN 20345:2011 S3 CI SRC

### All terrain safety boot

- Lightweight
- Flexible
- All terrain sole profile
- Excellent shock absorption
- Water resistant leather
- Antistatic
- 100% non-metallic
- Sizes : 36 - 48

**100%  
metal  
free**



### APPLICATIONS //

Outdoor work, building and construction, general industry, energy, logistic, maintenance, utilities, damp working conditions

### TECHNICAL SPECIFICATIONS //

- **PU20 sole:** very lightweight, highly flexible, excellent shock absorption, grip SRC | oil, hydrocarbon and chemical resistant, antistatic | grooves at the back of the heel for a better grip when the heel first touches the ground and deep grooves for better grip in the forefoot area | pronounced heel and GRIPSTEP profile for ladders and stairs | injection moulded PU scuff cap
- **Upper:** water-resistant black oiled grain leather, microfiber insert, reflective elements, non-metallic eyelets and hooks, reduced number of seems for better water resistance and less pressure points.
- **Quarter lining:** polyester mesh 3D, excellent breathability, quick drying
- **Vamp lining:** non-woven for excellent abrasion resistance
- **Tongue:** water resistant and padded, with gussets to keep dirt and debris out
- **Collar:** soft and compact foam for better comfort and protection
- **Composite toe cap:** antimagnetic, lighter than a conventional steel toe cap, conducts less heat and cold than a metal toe cap
- **Composite penetration resistant midsole:** flexible | antimagnetic | protects 100 % of the surface of the foot (as opposed to 85 % on average for steel soles) | lighter than steel soles | conducts less heat and cold than a metal sole
- **Hygienic insole:** removable, anatomically shaped, bottom layer open cell foam: good moisture absorption and wicking properties, quick drying
- French (EU) sizing system, width 11
- **Sizes :** 36-48
- **Weight:** 640 g per foot, in size 42